


# Endumax UV resistance

TEIJIN


ALLPLAST



EnduMax®

# Endumax Aging: 65°C, 80%RH


Tensile strength measurements at room temperature



# Endumax aging: 80°C, 90%RH



Tensile strength measurements at room temperature




# Short time heating



Placed Endumax tape and UHMWPE-fiber without tension in a hot air oven for 5 minutes at various temperatures. Tensile strength measurements at room temperature.




Short time heating: strength retention vs temperature



# Thermal Shrinkage

**TEIJIN**  
**ALLPLAST**



Tape (or fiber) is heated under pretension for 2 minutes in a Lenzing Thermal Shrinkage tester.

**EnduMax<sup>®</sup>**

Connect and Protect